



## Impulse 2NO Pushbutton

SVN331

### Technical Properties

Tightening torque	1,7Nm
Rated operational voltage Ue	230 V
type of connection	with screw
Connection cross-sect. flexible cable	0,75 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 10mm <sup>2</sup>
European directive RoHS	voluntary compliance
European directive WEEE	not concerned
Frequency	50/60 Hz
Operating temperature	-20 to 50 °C
Storage temperature	-40 to 80 °C
Protection index IP	IP20