



ENGLISH

Datasheet

RS Pro Non-Corrosive 10W 2ft Emergency Luminaire

RS Stock No: 124-8920



This RS Pro LED 10 W emergency luminaire has a 2 foot tube that can work on 230 V. The emergency tube has all the control gear and batteries are built into the tube. It can intelligently detect the difference between power failures and deliberately switches off the power.



ENGLISH

Typical Properties

Wattage	10 W
Beam Angle	120°
Lumen Output	900 Lm, 200 Lm in EM mode
Lamp Type	LED
Voltage	240 V
Colour Temperature	6000K
Operating Temperature	-10°C to +40°C
Lamp	T8 2FT
Lifetime hours	30000