


DIMENSIONS (IN.) No. OF В С D Α **PINS** 1.265 1.850 0.628 1.300 9 2.314 15 1.580 0.639 1.300 25 2.130 2.840 0.650 1.300

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (3) HOUSING SCREWS & NUTS (#4-40, RECOMMENDED TORQUE 5.2 in-lbs)
- (2) THUMBSCREWS (#4-40, RECOMMENDED TORQUE 60 in-oz)
- (1) GROMMET TREE (NON-CONDUCTIVE) [162-000-925R000]



MATERIAL: DIE-CAST ZINC ALLOY, NICKEL PLATED

OPERATING TEMPERATURE: -45°C TO +120°C

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:
02/16/2007

UNITS = inch

DO NOT SCALE FROM DRAWING



SCALE: SHEET OF REV 6

DWG NO. 981-YYY-130R121