

5988/INOX

		art.
	059880700	

- n. 2 **34INOX:** 160 - 200 mm
- n. 6 **96BPINOX/B6:** 2,5 - 3 - 4 - 5 - 6 - 8 mm
- n. 9 **42INOX/SC9:** 8 - 10 - 11 - 12 - 13 - 14 - 15 - 17 - 19 mm
- n. 1 **1048INOX:** 250 mm
- n. 1 **1150INOX:**  180 mm
- n. 1 **1370INOX:** 500 g
- n. 1 **1377INOX:** 230 g
- n. 5 **96TINOX:**  2,5 - 3 - 4 - 5 - 6 mm
- n. 15 **920INOX-A:**  10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 - 27 - 30 - 32 mm
- n. 1 **920/55INOX:** 
- n. 4 **1290INOX:**  3x75 - 4x100 - 5,5x150 - 6,5x150 mm
- n. 3 **1292INOX:** Phillips® screwdrivers  PH0x60 - PH1x80 - PH2x100 mm
- n. **VP-3SC:** thermoformed trays, empty
- n. **VP-LS:** thermoformed trays, empty

