

11107
Abrasive shaft-mounted wheels, abrasive pink corundum grains, ceramic bonded, trapezoidally shaped
EN 12413

For universal use

shaft Ø 6 x 40 mm

	art.	Ø mm	h mm	max. rpm Lo=13 mm	
111070012	11107 12X20	12	20	79.500	AR60P5V
111070015	11107 15X25	15	25	60.400	AR46P5V
111070020	11107 20X30	20	30	38.900	AR46P5V
111070025	11107 25X40	25	40	23.300	AR36/46P5V

