



Connection Units

Description

Metalclad offers a tough and impact resistant range of accessories with a durable finish and protective coating.

Each product is supplied with a surface mount metalclad back box and in its own polybag, protecting it up to the point of installation.

Features

- Durable and tough finish with protective coating
- Supplied complete with surface mounting box with knockouts
- Neon and flex outlet options
- Captive and backed out terminals
- Captive fuse carrier
- Terminals have clearly embossed markings
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- Neon leads enclosed
- Recessed earth bar
- Angled terminals to aid installation
- 2 earth terminals
- 25-year guarantee

Range

Unswitched Spur	VM1360
Unswitched Spur with Neon	VM1361
Unswitched Spur with Flex Outlet	VM1362
Switched Spur	VM1370
Switched Spur with neon	VM1371
Switched Spur with Flex Outlet	VM1372
Switched Spur with Neon and Flex Outlet	VM1373

Technical Specification

Voltage rating	250Vac
Current Rating	13A
Contact gap	3mm

No user serviceable parts, except BS 1362 fuse links

Back Boxes

All knockouts are 20mm diameter.

	Sides	Back
1g	5	1

Standards

- BS 1363 Part 4
- Fuses – BS 1362

Terminal Capacity

	2.5mm ²	4mm ²	6mm ²	10mm ²
L & N	4	2	2	1