
suction cup ESS-25X75-ON Part number: 189417

FESTO







Data sheet

| Feature | Value |
|--|--|
| Nominal size | 6 mm |
| suction cup size | 25x75 mm |
| suction cup volume | 6.7 cm3 |
| Position of connection | on top |
| Assembly position | Any |
| Correlation to suction-cup holder | Size 5 |
| Suction cup shape | Oval, flat |
| Operating pressure | 0 0.95 bar |
| Nominal operating pressure | -0.7 bar |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Food-safe | See Supplementary material information |
| Ambient temperature | -10 70 °C |
| Retention force at nominal operating pressure | 92.5 N |
| Horizontal lateral force at nominal operating pressure | 125.5 N |
| Vertical lateral force at nominal operating pressure | 115 N |
| Product weight | 46.8 g |
| Mounting type | Via vacuum port |
| Vacuum connection | M10 |
| Colour | Black |
| Shore hardness | 50 +/- 5 |
| Materials note | Free of copper and PTFE |
| | Conforms to RoHS |
| Material suction cup | NBR |