

FEATURES

- Hexagonal threaded standoff
- M3 threading on both sides
- Female/female configuration
- Length 10 mm
- Nylon 6 construction for durability
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007 Electrostatic Control Standards

HEX. THREADED SPACER 6I/10

RS Stock No.: 102-6362



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This threaded standoff is a convenient way to securely lock PCBs (printed circuit boards) into place. The standoff acts as an insulating guard between components to prevent electrical shorts. A hexagonal outer shape means it can be fastened easily using a standard spanner. The 10 mm long standoff is available in female-female configuration with M3 threading on both sides. As its part of our own RS PRO brand, this threaded standoff has been rigorously tested by engineers to ensure quality and consistency.

General Specifications

Gender Type	Female/Female
Material	Nylon
Body Shape	Hex
Application	Insulating guard between components to prevent electrical shorts

Mechanical Specifications

Body Length	10mm
Thread Size	M3

Approvals

Compliance/Certifications	ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007
---------------------------	---

