

Datasheet

Conquer Cartridge Fuse, F, 0.1A, 5 x 20mm

RS Stock No: **563-374**

Part Number: **VBS USL 250mA 250V (05)**



Product Details

Conquer cartridge fuse is current rated for 0.1 A. This F-speed fuse has Littelfuse time lag ceramic body that makes it ideal for applications when surge withstand is required.

Specifications:

Body Material	Ceramic
Breaking Capacity (at Maximum Voltage Rating)	1500 A
Current Rating	0.1 A
Diameter	5.2 mm
Fuse Speed	F
High Rupture Capacity	Yes
Includes Indicator	No
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Resistance	6.3375 Ω
Size Designation	Miniature
Voltage Rating	250 V ac
Standards Met	CSA Acceptance, UL Recognised, RoHS Compliant, VDE, BSI, CQC, KTL, SEMKO Approved
UL File Number	E82636