



Datasheet

RS PRO Double Sided PVC Tape

38mm x 50m

Stock number: 2175256

EN



General Description

The tape is a white PVC film coated on both sides with a clear, aggressive dispersion acrylic adhesive interleaved with a white siliconised paper release liner. The tape offers long lasting adhesion to joined surfaces and is easy to apply. Ideal for permanent fitting of rubber backed carpets and underlays and vapour control applications.

Features

- Very high tack
- Easy tear
- Flexible

Technical Details	Typical Values
Thickness	0.18 mm
Breaking Load	18 N/cm
Elongation	125%
Adhesion to steel faced side	12.0 N/cm
Adhesion to steel unfaced side	12.0 N/cm
RoHS compliant	Yes
Service Temperature	0°C to +70°C
Application Temperature	0°C to +40°C
Storage Temperature	+12°C to +25°C

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

