



Cut

Our best Cut Sleeves, now made green

- **Heightened defenses:** HyFlex® 11-250 is designed with INTERCEPT™ Cut Resistance Technology, meeting ANSI/ISEA 105-2024 CUT A3 and EN ISO B standards for arm protection.
- **Elevated comfort:** Their seamless HPPE yarn offers users a cool, breathable feel, while their bicep cuff keeps them securely in place
- **Reduced contaminant risks:** The risk of contaminant transfer to metal before painting is reduced, as they are silicone-free
- The HyFlex® 11-250's over-edges come in red, black or light blue, for narrow, wide or extra-wide
- **Food handling compliance:** HyFlex® 11-250 sleeves comply with FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600
- **Certified harm-free:** Oeko-Tex® certification indicates they are free of substances harmful to human health
- **Sustainable design:** HyFlex® 11-250 sustainable sleeves are designed with 37% recycled content* reducing our carbon footprint by 102g CO2eq/piece**

*% is the minimum recycled content in final product

** vs standard nylon sleeve



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Press shop operations
- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Handling structural and body components
- Inspection, selecting, checking parts
- Glass repair and replacement
- Seizing structural and body parts
- Body Surface checking, marking and touching up
- Adjusting systems and screwing
- Adjusting panels parts components

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-250

The most comfortable sleeve with Intercept technology

Key Features

- **INTERCEPT™ Cut Resistance:** ANSI/ISEA 105-2024 CUT A3 and EN ISO B protection
- **HPPE yarn:** Arm protection sleeves that ensure a cool, breathable feel
- **Silicone-free:** Avoiding contaminant transfer to metal prior to painting\
- **Sleeve made with 37% recycled content*:** Carbon footprint reduction of 102g CO2eq/piece**

*% is the minimum recycled content in final product

** vs standard nylon sleeve

Technologies



INTERCEPT™
Cut Resistance Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2X42B



STANDARD

100

4419CIT
CITEVE

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 11-250	Liner Material: Ansell INTERCEPT™ Technology Cuff Style: Knitwrist without thumbslot	15	Wide, Extra Wide	12" (30 cm), 16" (40 cm), 18" (45 cm)	50 sleeves/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell