




**Part Number :** [191930167](#)  
**Product Description :** VersaKrimp Ring Tongue  
Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud  
Size 3/8" (M9), Carton  
**Series Number :** 19193  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** D-351-38

Documents & Resources

**Drawings**  
[191930167 sd.pdf](#)  
**Specifications**  
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	800755050172

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	3.193/g
Packaging Type	Carton
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	7.19mm max.
Wire Size (AWG)	8
Wire Size mm <sup>2</sup>	8.36

---

## Application Tooling

### Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900001</u>
Manual Tool for Crimping Non- insulated 8 AWG thru 4/0 Terminals	<u>192940008</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
RHT1080 Hand Crimp Tool	<u>640034400</u>
Square "DIN" style dies for 8 AWG	<u>640037670</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640074400</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>