

VDV II





Voice, Data and Video Cable Verifier More than just a wiremapper



Ordering Information

| VDV II Range | |
|----------------|---|
| Part No. | Kit Contents |
| R158000 | VDV II – Voice, Data and Video Cable Verifier. Includes 1 x tester, 1 x dual port remote unit, 1 x coax remote unit, 1 x alkaline battery, 1 x multi-language user guide. |
| R158002 | VDV II Plus – Voice, Data and Video Cable Verifier. Includes 1 x tester, 1 x dual port remote unit, 1 x coax remote unit, 1 x alkaline battery, 1 x multi-language user guide, 2 x RJ45 to alligator clip cable 390mm, 2 x screened RJ45 to RJ45 cable 150mm, 2 x RJ11/12 to RJ11/12 cable 100mm, 1 x F-type plug to F-type plug cable 230mm, 1 x F-81 barrel splice, 1 x BNC female to F-type male adaptor, 1 x BNC female to F-type female adaptor, 1 x RCA female to F-type male adaptor, 1 x RCA female to F-type female adaptor, 1 x wallet wiring card, 1 x carry case. |
| R158003 | VDV II Pro – Voice, Data and Video Cable Verifier. Includes 1 x tester, 1 x dual port remote unit, 1 x coax remote unit, 1 x alkaline battery, 1 x multi-language user guide, 2 x RJ45 to alligator clip cable 390mm, 2 x screened RJ45 to RJ45 cable 150mm, 2 x RJ12 to RJ12 cable 100mm, 1 x F-type plug to F-type plug cable 230mm, 1 x F-81 barrel splice, 1 x BNC female to F-type male adaptor, 1 x BNC female to F-type female adaptor, 1 x RCA female to F-type male adaptor, 1 x RCA female to F-type female adaptor, 1 x wallet wiring card, 1 x carry case. |

Optional Accessories

| Part No. | Kit Contents |
|---------------|---|
| 158050 |  Kit of 12 x RJ45 remote units* (#1 - #12) |
| 158051 |  Kit of 24 x RJ45 identifiers** (#1 - #24) |
| 158053 |  Kit of 12 x coax remote units* (#1 - #12) |
| 62-164 |  Amplifier Probe |

* Separate numbered remotes allow multiple cables to be tested more quickly

** Multiple identifiers simplify cable labelling at the patch panel

Basic Specifications

| Dimensions (mm) | Weight | Length Range | Battery Type |
|-----------------|---------|--|--|
| 160 x 76 x 36 | 0.26 kg | 0.3 - 450m / 1-1476 ft (Plus and Pro only) | 9V alkaline. Typically 20 hours minimum continuous use (backlight off) |

For detailed specifications, please visit our website.



www.vdvii.com

IDEAL INDUSTRIES NETWORKS DIVISION
Unit 3, Europa Court, Europa Boulevard, Warrington,
Cheshire, WA5 7TN, UK.
Tel. +44 (0)1925 444 446 | Fax. +44(0)1925 445501
uksales@idealnwd.com

www.idealnwd.com



A subsidiary of
IDEAL INDUSTRIES INC.



Specification subject to change without notice. E&OE
Printed in UK.

© Ideal Networks 2014
Publication no. 158805 Rev 2.