

## Polyurethane General Use Tubing, Standard Inch Size - TIUB TIUB05BU-20

### Datasheet

- Applicable tubing O.D.: 1/8" to 1/2"
- Operating temperature: -20 to 60 °C for air and 0 to 40 °C for water
- 29 colour variation.

### Standard specifications

|                             |                                            |
|-----------------------------|--------------------------------------------|
| Size                        | 05 (ODØ4.76 IDØ3.18)                       |
| Color                       | BU (Blue)                                  |
| Roll Length                 | 20 m                                       |
| Reel Length                 | None                                       |
| Suffix                      | None                                       |
| Pressure medium             | Air, Water                                 |
| Maximum operating pressure  | 0.8 MPa                                    |
| Maximum ambient temperature | 60 °C / 40 °C for Water                    |
| Minimum ambient temperature | -20 °C (with no freezing) / 0 °C for Water |
| Weight                      | 0.420 Kg                                   |

## Additional information

Catalogue

[TU-29COLOR-A\\_EU.pdf](#)