


**06700030**

RCK 70 - Self centring

**2D Technical Drawing**

**Dynamic 3D View**
**Technical Specifications**

Part number (CODE)	06700030
Ød (DD) mm	30
ØD (D) mm	55
L1 (L1) mm	26
L2 (L2) mm	31
L3 (L3) mm	39
L (L) mm	45
Maximum torque Mt (MT) Nm	760
Clamping pressure - Shaft (CPS) N/mm <sup>2</sup>	200
Clamping pressure - Hub (CPH) N/mm <sup>2</sup>	120
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	6
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x25
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	17
Extraction thread - Type (ETT)	M6
Extraction thread - Num. (ETN)	3
Weight (WEIGHT) kg	0.45