



Main

Range	Rilux
Product name	Rilux LED
Product or component type	Emergency light fitting
Function	Standard
Supply	Maintained
Light source	LED 0.3 W x 8
Number of batteries	1 x 3.6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Wiring device additional information	Pictograms to be ordered separately

Complementary

[Ue] rated operational voltage	230 V 50 Hz
Power consumption in VA	24 VA
Electrical insulation class	Class II
Autonomy	1 h 30
Charging time	12 h
Luminous flux	Emergency condition: 170 lm Maintained mode: 120 lm
Device mounting	Surface ceiling Flush false ceiling Wall mounted wall
Height	51 mm
Width	343 mm
Depth	104 mm
Net weight	0.59 kg

Environment

IP degree of protection	IP40
IK degree of protection	IK06
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Standards	IEC 50-11

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	614 g
Package 1 Height	5.4 cm
Package 1 width	10.4 cm
Package 1 Length	34 cm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------