

305mm General-Purpose Solid Stem Thermometers with White-backed Glass. Stirring bulbs. Mercury filled. Non-roll fittings. Order in tens.

Range	Division	Product No.	
		76mm Immersion	Total Immersion
-35/50C	1	40/400	40/400/1
-10/50C	0.5	40/401	40/401/1
-10/110C	1	40/403	40/403/1
-10/110C	0.5	40/803	40/803/1
-10/150C	1	40/406	40/406/1
-10/200C	1	40/408	40/408/1
-10/250C	1	40/410	40/410/1
-10/300C	1	40/412	-
-10/360C	2	40/414	40/414/1
-10/400C	2	40/416	-
50/550C	2	46/454	-
-30/120F	1	40/402	-
0/230F	1	40/404	-
30/400F	2	40/409	-
-10/110C & 0/230F	1 & 2	42/403	-
-10/250C & 0/500F	1 & 2	42/410	-
-10/360C & 0/700F	2 & 5	42/414	-

RS 206-8806 = 40/401
 RS 208-6438 = 40/403
 RS 206-8812 = 40/406
 RS 206-8834 = 40/414

155mm Stirring Thermometers. Mercury filled. Order in tens.

-10/50C	1	-	40/450
-10/110C	1	-	40/430
-10/250C	5	-	40/448
-10/360C	5	-	40/452

RS 206-8862 = 40/430 MERCURY VERSION
 RS 206-8878 = 44/430 SPIRIT VERSION OF 40/430

305mm Red Spirit Filled Stirring Thermometers with white-backed glass. Stirring bulbs. Non-roll fittings. Order in tens.

Range	Division	Imm.	Product No.
-10/50C	0.5	76mm	44/401
-10/110C	1	76mm	44/403
-10/150C	1	76mm	44/406

RS 206-9297 = 44/401
 RS 206-8840 = 44/403
 RS 206-8856 = 44/406

Slot Cases for Laboratory Thermometers. Screw caps.

Thermometer Length	Product No.
Brass	
155mm	47/732/0
205mm	47/632/0
255mm	47/532/0
305mm	47/432/0
355mm	47/832/0
405mm	47/932/0

RS 206-8890 = 47/732
 RS 206-8884 = 47/432