

Features

- Accepts cable diameters of upto 20mm
- Can be used with a maximum panel thickness of upto 2mm Thick.
- REACH and ROHS Compliant

RS PRO Black Polychloroprene 28mm Open Cable Grommet for Maximum of 20mm Cable Dia

RS Stock No.: 0428019



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This 28 mm round open cable grommet from RS PRO is designed for easy installation, providing protection for wires while ensuring a tidy finish. To use, simply cut a hole to the required size, insert the grommet into the panel, and feed the cable through the pre-formed opening.

It accommodates cables with diameters between 1 mm and 20 mm, offering a secure and flexible routing solution. This grommet is compatible with panels up to a maximum thickness of 2 mm, helping to reduce cable strain and minimise wear.

Made from black polychloroprene rubber, it is suitable for temperatures ranging from -30°C to +90°C.

Specifications

Grommet Type	Open Cable Grommet
Material	Polychloroprene
Colour	Black
Maximum Panel Thickness	2mm
Minimum Cable Diameter	1mm
Maximum Cable Diameter	20mm
Panel Hole Diameter	28mm
Minimum Operating Temperature	90°
Maximum Operating Temperature	-30°

Approvals

Standards Met	REACH, RoHS
---------------	-------------