



Image may differ from product. See technical specification for details.

PHG C54

Wrapped classical V-belt

Belts provide a very efficient and cost-effective method for transmitting power from prime movers to driven machines. Classical V-belts have pre-tensioned polyester cords that provide low stretch during operation and a fibre-loaded rubber cushion that gives good transverse rigidity. Being fully wrapped in a heavy duty industrial fabric, the belts have a high resistance against abrasion.

- High flexibility
- Low elongation during operation
- Oil and heat resistant, with anti-static properties
- Fully wrapped to resist abrasion
- Reduced energy consumption and increased mean time between failures

Overview

Dimensions

Height	14 mm
Inner length	1 372 mm
Pitch length	1 430 mm
Width, top	22 mm

Properties

Cogged	No
Material	CR (polychloroprene)
Section	C
Tensile cord	Polyester
Wrapped Cover	Yes

Logistics

Product net weight	0.39 kg
eClass code	23-17-02-90
UNSPSC code	26111504



Terms of use