

Technical data sheet

Article number:
111-04891

T50R



Product Group	Cable ties for higher impact resistant polyamide 6.6 ScanBlack
Product Family	T-Series in PA66HIR(S)
Material	Polyamide 6.6, high impact modified, scan black (PA66HIR(S))
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 HB
Halogen-free	Yes
Length (L)	200 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +80 °C
Package Content packed in	bag
Pack Cont.	500 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
UV-resistant acc. to ASTM D6779 (Yes/No)	No
Variant	Inside Serrated
Weight/Unit	0.0013 kg
Width (W)	4.6 mm

