

EKH 30-G-2FSH



Sample image

Order symbol : EKH 30-G-2FSH

Product nr : 3530147

Description : Hinged cover, PC

Remarks : Grey

EAN : 6418074040541

El. number :

- Finland : 3420787
- Denmark : 8212012723
- Sweden : 2538220

Dimensions :	Height	Width	Depth
mm :	190	190	30
inch :	7.48	7.48	1.18

Materials :

Material :	Polycarbonate
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C