Features

- Universal Process Input (TC, RTD, mVdc, Vdc, mAdc) Type
- 4 Digits (PV) Display
- 100...240Vac Power Supply
- Process Output Relay (5A@250Vac)
- ModBus RS-232 RTU Serial Communication
- 72X72mm Panel Dimension

RS PRO Process Controller

RS Stock No:
874204



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Process Controller

Product Description

Process Controller
Universal Process Input (TC, RTD, mVdc, Vdc, mAdc) Type
1X Process Output, Relay (5A@250Vac)
ModBus RS-232 RTU Communication
Applications Fields
- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications

General Specifications

Supply Voltage and Power	100…240Vac 50/60Hz – 2,5A
Sensor Inputs	TC, RTD, mVdc, Vdc, mAdc
Output (Process)	1 Relay Output (5A@250Vac) at resistive Load
Communication	ModBus RS-232 RTU
Accuracy	Scale ± %0.25

Mechanical Specifications

Dimension	72 mm x 72 mm 87,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

