

## eco!Booster TR 036

eco!Booster with 50% higher area performance than the Kärcher power nozzle; ideal for delicate surfaces. For cold and hot water high-pressure cleaners (nozzle size 036).



Order no. **2.113-083.0**

### Technical data

EAN code		4066529118301
Pressure	bar	max. 300
Temperature	°C	max. 85
Nozzle size		36
Connection thread		EASY!Lock
Weight incl. packaging	kg	0.5



## 50% higher cleaning performance compared to the flat jet

- Thorough, fast and more sustainable cleaning.

## 50% higher water efficiency\*

- Saves water.
- \* Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

## 50% higher energy efficiency\*

- Saves energy.
- \* Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

## COMPATIBLE MACHINES

- HD 5/11 E Classic
- HD 5/11 EX Plus Classic
- HD 5/12 C
- HD 5/13 E Classic
- HD 5/13 EX Plus Classic
- HDS 6/14 C