

ELECTRONIC SERVICE—CASE SECURITY 6750

A case with the basic equipment of special tools for the installation and maintenance of complex protective devices and alarm systems



6750 **BERNSTEIN SECURITY** with tool set

6755 **BERNSTEIN SECURITY** without tool set

Description:

Case made from deep-drawn, impact-resistant, grained black plastic, with sturdy aluminium frame, dustproof and rainproof, acid- and scratch-resistant. 64 tools are clearly arranged on two removable tool trays, one of it on both sides, and in the bottom tray with adjustable partitions. Further tools or accessories can be lodged in the tray until 60 mm height. The basic equipment for special operations at protective devices and alarm systems may efficiently be completed by special tools additionally recommended. The case has 2 locks.

Outside dimensions: 470 x 340 x 170 mm

Weight without tools: ca. 4.600 kg

Weight with tools: ca. 8.400 kg

Tool set:

No.	Description of individual tools
2-265	2 Test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire
2-701	Insertion tool with sensor for connecting the wires and simultaneously cutting of the residual wire
2-705	Contactless voltage detector VOLTtester
3-112-2	Side cutters , 120 mm, for soft wire up to 1.0 mm Ø; with rounded head, without side face, double leaf spring, chrome-plated, with dip insulation
3-0611	Crimping pliers , for BNC- and TNC-coaxial connectors
13-906 VDE	VDE Side cutters , 160 mm, for steel wire up to 1.6 mm Ø; chrome-plated, VDE safty insulation
13-915 VDE	Telephone pliers , 160 mm, chrome-plated, VDE safty insulation
13-927 VDE	Flat nose pliers , 160 mm, with long jaws, chrome-plated, VDE safty insulation
13-936 VDE	Combination pliers , 160 mm, chrome-plated, VDE safty insulation
4-431	Retaining screwdriver , for inserting and tightening slotted screws, blade made for CV, burnished, insulated, blade 100 x 3.0 mm
4-437	Retaining screwdriver , for inserting and tightening cross-recess screws size 1, blade made for CV, burnished, insulated
14-651 VDE	Screwdriver , with VDE insulation, blade 75 x 2.5 mm
14-652 VDE	Screwdriver , with VDE insulation, blade 100 x 3.5 mm
14-653 VDE	Screwdriver , with VDE insulation, blade 100 x 4.0 mm
14-681 VDE	Cross-recess screwdriver , size 0, VDE, blade length 60 mm
14-682 VDE	Cross-recess screwdriver , size 1, VDE, blade length 80 mm
14-683 VDE	Cross-recess screwdriver , size 2, VDE, blade length 100 mm
14-684 VDE	Cross-recess screwdriver , size 3, VDE, blade length 150 mm
5-505	Insulation stripping tool , with hook blade, for cable Ø 4 - 28 mm
5-515	Universal blade knife
5-531	Automatic wire stripper Super , for all common stranded and solid conductors of 0.2 - 6.0 mm ² , adjustable length stop of 5 - 12 mm, built-in side cutters for max. Ø 2 mm

No.	Description of individual tools
5-535	Coax cable stripper for Coax cable Ø 4.8 - 7.5 mm
6-103	Socket wrench , with special BERNSTEIN square handle, blade made from CV, chrome-plated, SW 4,5 mm
6-104	Socket wrench , as above, AF 5.0 mm
6-105	Socket wrench , as above, AF 5.5 mm
6-600	Combination ring- and open-ended wrench , 7-piece set, CV, chrome-plated, 6,0, 7,0, 8,0, 9,0, 10,0, 11,0, 13,0 mm
6-880	Hexagon wrench keys , 8-piece set in a wallet, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
6-950	Ballpoint wrench keys , hexagon, 8-piece set in a wallet, 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0 mm
6-995	TORX screwdrivers with bore-hole in the tip , 8-piece set in a box, T 9, T 10, T 15, T 20, T 25, T 27, T 30, T 40
7-116	Engineer's hammer to DIN 1041, 300 g
7-425	Dust brush
7-506	Roller tape measure , 2 m
7-535	Spirit level , 225 mm long
7-616	Pocket hack saw PUK , with adjustable handle in a wallet
8-375	ERSA gas soldering iron , Independent 75
8-385	ERSA desoldering pump OVAC X

To complete the set we recommend:

2270	Service Set ACCENT , 9-piece set with ESD tools
4-222	Screwdriver , blade 260 x 3.0 mm
4-227	Cross-recess screwdriver , size 1, blade length 300 mm
4-228	Cross-recess screwdriver , size 2, blade length 300 mm
4-920	Interchangeable screwdriver set with ESD-handle, 9-piece, Slot 1.5/3.0 mm, 2.0/3.5 mm und 2.5/4.0 mm, KS Gr. 000/00, 0/1, TORX T 5/T 6, T 7/L/T 8L, T 9/L/T 10L, ("L" with bore hole)