



Disposable

# SOLO BOX 967

Compromis between dexterity and resistance.



CHEMICAL PROTECTION  
**TYPE C**

EN ISO 374-1



TYPE C

EN ISO 374-5



DEXTERITY  
EN ISO 21420:  
5/5

CATEGORY 3



0334

## SPECIFIC ADVANTAGES



### Comfort

- Excellent dexterity thanks to flexibility and reduced material thickness



### Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

## INDUSTRIES

- Automotive/mechanical industry
- Mechanical industry
- Laboratory

## APPLICATIONS

- Assembly of small oily parts
- Manufacturing of medicines
- Pharmaceutical preparation
- Research, analysis, handling of precision parts



Disposable

# SOLO BOX 967

## LEGENDS

EN ISO 374-1

CHEMICAL RISKS



TYPE C

EN ISO 374-5

MICRO-ORGANISMS

Protection against bacteria and fungi



## PRODUCT DETAILS

Interior finish	Non powdered
Exterior finish	Smooth with pebbled fingertips
Material	Nitrile
Cuff characteristic	Rolled Cuff
Colour.s	Blue
Length (cm)	25
Thickness (mm)	0.08
European sizes	6 7 8 9
AQL Liquidproofness	< 1.5

## LOGISTIC DETAILS

Packaging	100 gloves/box 1000 gloves/carton
-----------	--------------------------------------

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/02/19/0583
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France