

RJ45FC6-FW

Article Number: 852-25069

Category 6 Modular Keystone Jack, Office White, 1/bag



Base Data

Local Order Number RJ45FC6-FW

Type RJ45FC6-FW

Color Office White (OEWH)

- Features and Benefits**
- Category 6 jack has been uniquely designed adopting HellermannTyton's globally tried and tested 10-Pin technology which guarantees superior performance and connectivity.
 - Standard keystone style interface provides flexibility in connecting components.
 - Unique strain relief design secures cable terminations.
 - Configured to both TIA 568A and 568B wiring schemes for installation versatility.
 - Available in 12 colors for easy color coding identification.

Product Description HellermannTyton's GigaBand flush Category 6 modular jack is designed to "future proof" installations. Its patented design uses innovative crosstalk-cancellation technology. The performance of the GigaBand system provides significant margin over TIA Category 6 (ANSI/TIA-568-C.1) and ISO Class E (ISO/IEC-11801, 2nd edition) requirements. The GigaBand system will easily support applications such as Gigabit Ethernet. ETL tested and approved for Category 6 component compliance.

Performance Category Category 6 (Class E)

Port count 1

Sub Category Jack

Technical Description The performance of the Cat6 system provides significant margin over TIA Cat6 and ISO/IEC 11801 requirements.

Short Description Category 6 Modular Keystone Jack, Office White, 1/bag

Product Dimensions

Width W (imperial) 3.75 "

Width W (metric) 19.0 mm

Height H (imperial) 3.91 "

Height H (metric) 23.0 mm

Depth D (imperial) 1.65 "

Depth D (metric) 42.0 mm

Logistics and Packaging

Quantity per bag

Package Quantity (imperial) 1

Package Quantity 1

Carton Quantity 50

Material and Specifications

