



Cut

Ergonomic Protection



Heat



Medium Duty

Protective gloves with superior grip, ensuring cut and oil resistance

- **Advanced defenses:** HyFlex® 11-928 industrial gloves grant a glass-free, aramid liner that is designed with INTERCEPT™ Technology to provide advanced cut resistance
- **Specialized protection:** Free from silicone and DMF, these abrasion-resistant gloves ensure optimal personal protection and prevent contamination of metal before painting
- **Enhanced grip:** These safety gloves deliver high grip performance for safer handling in dry to slightly oily applications
- **Improved durability:** In addition, these mechanical protection gloves feature a double-dipped, RIPEL™ Technology-enhanced, nitrile coating that guards against oil and industrial fluid exposure, while providing high durability and longer wear life
- **Added safety:** For enhanced workplace safety, these HyFlex® gloves also offer Level 1 Contact Heat Protection



Industries

- Automotive
- Metal fabrication
- Machinery and Equipment
- Oil and gas

Applications

- General maintenance
- Handling sharp or irregular metal pieces
- Handling of glass sheets, sharpened objects
- Grinding
- Machining / Stamping / Cutting

Key Features

- **Glass-free liner made with INTERCEPT™ Technology:** Enhanced cut protection
- **Silicone- and DMF-free:** Prevents metal contamination prior to painting
- **Reliable grip:** Safer handling of dry to slightly oily applications

Technologies



DMF free



Fibre glass free



Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-928	Finishing: ¾ Dipped Coating Material: Nitrile Liner Material: Ansell INTERCEPT™ Technology, Aramid Cuff Style: Knitwrist	15	7, 8, 9, 10, 11	236-265mm/9.3-10.4 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699