

Datasheet

ENGLISH

Spring Loaded Index Plunger with Locking Rest Position

Knob material

High impact resistant thermoplastic

Knob finish

Matt

Body material

Burnished steel or stainless steel


Standard colour

Black knob

Options

Comes as standard with 90° locking rest position in plunger body.





| Part No. | Α | В | С | D | E | Thread size | Plunger diameter (mm) | Body material |
|----------|----|----|---|----|---|----------------|-----------------------------|-----------------|
| 237766 | 21 | 51 | 5 | 17 | 5 | M10x1.0 | 5 | Burnished steel |
| 237788 | 25 | 61 | 6 | 20 | 6 | M12x1.5 | 6 | Burnished steel |
| 237794 | 31 | 76 | 8 | 26 | 7 | M16x1.5 | 8 | Burnished steel |
| 237390 | 21 | 51 | 5 | 17 | 5 | M10x1.0 | 5 | Stainless steel |
| 237401 | 25 | 61 | 6 | 20 | 6 | M12x1.5 | 6 | Stainless steel |
| 237407 | 31 | 76 | 8 | 26 | 7 | M16x1.5 | 8 | Stainless steel |