

FEATURES

- Multi-function; 8 or 18 functions (depending on model)
- 17.5mm width
- 3-digit LCD display
- DIN Rail mounting
- Wide operating voltage; 24V-240V ac/dc
- 0.1s-999 h timing range
- Up/down counting modes
- Clear LED indication of relay status
- All settings programmed with only 2 keys
- Key lock function

RS PRO SPDT Multi Function Timer Relay - 01. s → 999 h, 1 Contacts, Multi Function, DIN Rail

RS Stock No.: 896-6863



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Timer Relays



Product Description

RS Pro LCD Digital time delay relay has the option of 8 or 18 functions depending on the model. It is built in a compact design for easy installation and has a digital display for easy viewing of run time and pre-set time.

General Specifications

Switch Configuration	SPDT
Mode of Operation	Multi-Function
Contact Configuration	1C/O
Number of Timer Functions	18
Number of Contacts	1
Time Range	01.s to 999 h
Time Increment	Hours, Minutes, Seconds
Applications	Production, Safety, On-delay timers, Off-delay timers, Interval-on-operate, Flasher, Repeat cycle

Electrical Specifications

Power Supply	External
Supply Voltage	24V to 240V ac/dc
Minimum Voltage	24V ac/dc
Maximum Voltage	240V ac/dc
Current Maximum	8A
Current Minimum	0.1A

Timer Relays



Mechanical Specifications

Mounting Type	DIN-Rail
Depth	76 mm
Width	17.5 mm
Length	89 mm

Operation Environment Specifications

Maximum Operating Temperature	55°C
Minimum Operating Temperature	-10°C

Protection Category

IP Rating	IP20; IP40
ir Katiliy	IFZU, IF4U

Approvals

Compliance/Certifications	CE, RoHS
---------------------------	----------







