

TAH2101G-160

ERGO™ Spring Side Cutting Pliers with Safety Ring 160 mm




PRODUCT DETAILS

- \bullet Side cutting pliers developed according to the scientific ERGO $^{\text{TM}}$ process
- ERGO™ handles with two-component combination, thermoplastic surface on tough polypropylene to give a superior grip
- Induction hardened cutting edges
- Progressive edges: The cutting radius progresses along the edge in order to cut hard material like piano wire close to the joint
- Soft materials like copper and plastic insulated wire at the tip
- Equipped with a patented return spring featuring an on/off function
- High performance alloy steel

- Phosphate finish, anti-corrosion treated
- ISO 5749
- Suitable for working at height
- Permanent stainless steel ring attached directly to the body of the plier maintains user ergonomics and full functionality
- Safety ring is attached to the metallic part to avoid losing handle
- Coloured tags with maximum weight for proper match with lanyard
- Compliant with DROPS best practices







PRODUCT ATTRIBUTES

Product	Α	В	C	D	E	(Cu	Fe+	Piano	g
TAH2101G-160	165 mm	20 mm	21 mm	11 mm	2 mm	3.8 mm	2.5 mm	2.0 mm	180 g