

Datasheet

RS Pro IP65 Anti-Vandal Push Button



Specifications:

- Terminal Type: Screw Terminals
- Actuator Shape: Domed with Yellow Ring
- Switching: 1NO Momentary
- Panel Cut Out: 16mm
- Switch Rating: 2A/36Vdc
- Contact Resistance: $\leq 50\text{M}\Omega$
- Insulation Resistance: $\geq 1000\text{M}\Omega$
- Dielectric Strength: 2000Vac
- Operating Temperature: $-25^{\circ}\text{C} \sim 55^{\circ}\text{C}$
- Mechanical Life: 1,000,000 Cycles
- Electrical Life: 200,000 Cycles

Specifications:

- Panel Thickness: 1 ~ 6mm
- Torque: 0.6Nm max.
- Operation Pressure: 4N approx.
- Operation Travel: 1.5mm approx.
- IP Degree: IP65
- Contact Material: Silver Alloy
- Button/Body Material: Stainless Steel
- Base Material: PBT

Dimensions:

Unit: mm

