


A FRONT VIEW





SIDE VIEW




BACK VIEW


PART NUMBER	LENGTH
USB3AU50CMRS	L=500±30
USB3AU1MRS	L=1000±50
USB3AU2MRS	L=2000±50



B FRONT VIEW



SIDE VIEW




BACK VIEW

USB 3.0 Standard-A to Micro-B Cable Assembly wiring

USB 3.0 Standard-A		Wire		USB 3.0 Micro-B	
Pin	Signal Name	Wire Number	Signal Name	Pin	Signal Name
1	VBUS	1	PWR	1	VBUS
2	D-	2	UTP_D-	2	D-
3	D+	3	UTP_D+	3	D+
4	GND	4	GND_PWRrt	5	GND
5	stdA_SSRX-	5	SDP1-	6	MicB_SSTX-
6	stdA_SSRX+	6	SDP1+	7	MicB_SSTX+
7	GND_DRAIN	7 and 10	SDP1_Drain SDP2_Drain	8	GND_DRAIN
8	stdA_SSTX-	8	SDP2-	9	MicB_SSRX-
9	stdA_SSTX+	9	SDP2+	10	MicB_SSRX+
Shell	Shield	Braid	Shield	Shell	Shield

④	USB 3.0 MICRO B MALE CONNECTOR, METAL SHELL NICKEL PLATED, INSULATOR, BLACK	1
③	USB CABLE, (30AWG*1P+D+AL+M)*2P+30AWG*1P+22AWG*2C +F+AB, DOUBLE SHIELDED, BLACK	1
②	PVC MOLDING HOUSING, BLACK	2
①	USB 3.0 TYPE A MALE CONNECTOR, METAL SHELL NICKEL PLATED, INSULATOR, BLUE	1
ITEM	DESCRIPTION	Q'TY

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB3AUxMRS
DESCRIPTION	Slim Micro USB 3.0 Cable - M/M - Right-Angle Micro-USB
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE: 10/19/2022	