



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	39						
			P2	REVISED PER ECO-11-010839	25MAY11	RK	HMR

D


C

B


A



- 1 PBT
2 LCP
3 TOLERANCE IS $+ .007 / - .003$ FOR 6 POSITION AND SMALLER SIZES.




3



$.025 \pm .003$

DETAIL FOR -1 ONLY
(2 POSITION)



$.025 \pm .003$

DETAIL FOR -2 ONLY
(3 POSITION)

2	2.595	2.520	2.400	24	25	2-103653-4
2	2.495	2.420	2.300	23	24	2-103653-3
2	2.395	2.320	2.200	22	23	2-103653-2
2	2.295	2.220	2.100	21	22	2-103653-1
2	2.195	2.120	2.000	20	21	2-103653-0
2	2.095	2.020	1.900	19	20	1-103653-9
2	1.995	1.920	1.800	18	19	1-103653-8
2	1.895	1.820	1.700	17	18	1-103653-7
2	1.795	1.720	1.600	16	17	1-103653-6
2	1.695	1.620	1.500	15	16	1-103653-5
2	1.595	1.520	1.400	14	15	1-103653-4
2	1.495	1.420	1.300	13	14	1-103653-3
2	1.395	1.320	1.200	12	13	1-103653-2
2	1.295	1.220	1.100	11	12	1-103653-1
2	1.195	1.120	1.000	10	11	1-103653-0
2	1.095	1.020	.900	9	10	103653-9
2	.995	.920	.800	8	9	103653-8
2	.895	.820	.700	7	8	103653-7
2	.795	.720	.600	6	7	103653-6
1	.695	.620	.500	5	6	103653-5
1	.595	.520	.400	4	5	103653-4
1	.495	.420	.300	3	4	103653-3
1	.395	.320	.200	2	3	103653-2
1	.295	.220	.100	1	2	103653-1
MATERIAL COLOR-BLACK	D	C	B	A	NO OF POSN	PART NUMBER

103653

B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 28JUL00	TE Connectivity			
DIMENSIONS: INCHES		CHK K WRIGHT 28JUL00				
		APVD K WRIGHT 28JUL00	NAME			
		PRODUCT SPEC 108-25034	PIN HOUSING, AMPMODU MTE, SINGLE ROW, .100 CL POLARIZED WITH LATCH			
MATERIAL SEE TABLE		APPLICATION SPEC 114-25026	SIZE A2	CAGE CODE 00779	DRAWING NO C=103653	RESTRICTED TO -
FINISH -		WEIGHT -	CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1
					REV P2	