USB Connector

Features



- Plug & Play capability
- Gold plated contacts
- Typical applications would include smartphones, tablets, PCs and cameras

Specification

Current Rating	1 A
Dielectric Withstanding Voltage	100 VAC
Contact Resistance	50 mOhm Max.
Insulation Resistance	100 MOhm min.
Temperature Range	-20 ... 85 °C
USB Connector Type	Micro USB-B
USB Standard	USB 2.0
Gender	Plug

Material Specification

Housing	Thermoplastic
Contact	Copper Alloy, Gold Flash Finish
Shell	SUS, Nickel Finish
Spring	SUS
Cover	Thermoplastic

Drawing

