

# HS LC-V-D3/ R3XC1-5,08-15 - Fiber optic



1531503

<https://www.phoenixcontact.com/gb/products/1531503>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiple light guides, passive, rigid, Cylinder head, emission surface: planar, number of displays: 3, (3 rows, 1 column), pitch: 5.08 mm, ESD protection: <12 kV, can be used for the BC housing range (housing must be processed)

## Your advantages

- Light guides are perfectly matched to electronics housings
- Easy mounting on the PCB using press pins
- Resistance to ESD
- Housing processing available on request
- Enables simple visual status and diagnostic indicators

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1531503       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 1,000 pc      |
| Sales key                            | ACGABB        |
| Product key                          | ACGABB        |
| GTIN                                 | 4067923160927 |
| Weight per piece (including packing) | 1.012 g       |
| Weight per piece (excluding packing) | 1.012 g       |
| Customs tariff number                | 90019000      |
| Country of origin                    | TN            |

## Technical data

### Notes

|               |                                                           |
|---------------|-----------------------------------------------------------|
| Assembly note | Please observe the application note in the download area. |
|---------------|-----------------------------------------------------------|

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Fiber optic           |
| Number of positions  | 3                     |
| Pitch                | 5.08 mm               |
| Number of rows       | 3                     |
| Alignment            | Vertical              |
| Type                 | passive, rigid        |
| Conductor type       | Multiple light guides |
| Head form            | Cylinder head         |
| Number of indicators | 3 (3 rows x 1 column) |

### Electrical properties

|                |         |
|----------------|---------|
| ESD protection | < 12 kV |
|----------------|---------|

### Dimensions

|               |         |
|---------------|---------|
| Diameter      | 3 mm    |
| Hole diameter | 2.4 mm  |
| Pitch         | 5.08 mm |

### Material specifications

|                                        |              |
|----------------------------------------|--------------|
| Flammability rating according to UL 94 | HB           |
| Insulating material                    | Polycarbonat |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Max. IP code to attain          | IP20             |
| Ambient temperature (operation) | -40 °C ... 85 °C |

# HS LC-V-D3/ R3XC1-5,08-15 - Fiber optic



1531503

<https://www.phoenixcontact.com/gb/products/1531503>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460404 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

# HS LC-V-D3/ R3XC1-5,08-15 - Fiber optic



1531503

<https://www.phoenixcontact.com/gb/products/1531503>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)