



ENGLISH

## Datasheet

Stock No: 563-699

# RS Pro Cartridge Fuse, T, 3.15A



## Product Details

Anti Surge (T) HBC – Ceramic Bodied, 5 x 20

Littelfuse Time lag ceramic body cartridge fuses are ideal for applications when surge withstand is required.  
Breaking capacity 1.5kA @ 250Vac

## Specifications:

Current Rating	3.15A
Diameter	5mm
Fuse Speed	T
Body Material	Ceramic
High Rupture Capacity	Yes
Breaking Capacity at Maximum Voltage Rating	1500 A
Operating Temperature Range	-55 → +125 °C
Voltage Rating	250V ac
Minimum Operating Temperature	-55°C
Maximum Operating Temperature	+125°C