



SS

KUNSTSTOFF-ABSTANDSROLLEN

| Artikel Nr. | | | | | | | Länge "L" mm | Länge "L" Toleranz | VPE |
|-------------------------|-------------------------|-------------------------|-------------------------|-------------------------|--------------------------|--------------------------|--------------------|--------------------------|------|
| "A" 3.1 mm ± 0,18 | "A" 3.7 mm ± 0,18 | "A" 4.5 mm ± 0,18 | "A" 4.5 mm ± 0,18 | "A" 5.1 mm ± 0,25 | "A" 6.8 mm ± 0,25 | "A" 10.1 mm ± 0,25 | | | |
| "B" 6.4 mm ± 0,18 | "B" 6.4 mm ± 0,18 | "B" 6.4 mm ± 0,18 | "B" 9.5 mm ± 0,18 | "B" 9.5 mm ± 0,25 | "B" 12.7 mm ± 0,25 | "B" 12.7 mm ± 0,25 | | | |
| SS-4-2 | SS-6-2 | SS-8-2 | SS-8-2L | SS-10-2 | SS-1/4-2 | SS-3/8-2 | 6.4 | 0.25 | 1000 |
| SS-4-3 | SS-6-3 | SS-8-3 | SS-8-3L | SS-10-3 | – | SS-3/8-3 | 9.5 | | |
| SS-4-4 | SS-6-4 | SS-8-4 | SS-8-4L | SS-10-4 | SS-1/4-4 | SS-3/8-4 | 12.7 | | |
| SS-4-5 | SS-6-5 | SS-8-5 | SS-8-5L | SS-10-5 | – | – | 15.9 | | |
| SS-4-6 | SS-6-6 | SS-8-6 | SS-8-6L | SS-10-6 | SS-1/4-6 | SS-3/8-6 | 19.1 | | |
| SS-4-8 | SS-6-8 | SS-8-8 | SS-8-8L | SS-10-8 | SS-1/4-8 | SS-3/8-8 | 25.4 | 0.38 | 500 |
| SS-4-10 | SS-6-10 | SS-8-10 | SS-8-10L | SS-10-10 | SS-1/4-10 | SS-3/8-10 | 31.8 | | |
| SS-4-12 | SS-6-12 | SS-8-12 | SS-8-12L | SS-10-12 | SS-1/4-12 | SS-3/8-12 | 38.1 | | |
| SS-4-14 | SS-6-14 | SS-8-14 | SS-8-14L | SS-10-14 | SS-1/4-14 | SS-3/8-14 | 44.5 | | |
| SS-4-16 | SS-6-16 | SS-8-16 | SS-8-16L | SS-10-16 | SS-1/4-16 | SS-3/8-16 | 50.8 | 0.51 | 500 |
| – | – | SS-8-18 | SS-8-18L | SS-10-18 | SS-1/4-18 | SS-3/8-18 | 57.2 | | |
| – | – | SS-8-20 | SS-8-20L | SS-10-20 | SS-1/4-20 | SS-3/8-20 | 63.5 | | |
| – | – | SS-8-22 | SS-8-22L | SS-10-22 | SS-1/4-22 | SS-3/8-22 | 69.8 | | |
| – | – | SS-8-24 | SS-8-24L | SS-10-24 | SS-1/4-24 | SS-3/8-24 | 76.2 | | |

Material: CPVC - hellgrau; UL 94 V-0, RMS-11
VPE: bitte Tabelle entnehmen.

Bestellinfo:

| | | |
|---------|-----|-------|
| SS | 6 | 14 |
| Artikel | Typ | Länge |