

VERSAFIT-1/4-0-SP

 SUPERSEDED

TE Internal #: 5058744001

TE Internal Description: VERSAFIT-1/4-0-SP

Mil-Spec: [M23053/5-306-0, M23053/5-106-0]

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #679857-2
CRIMPER, WIRE "F"



TE Part #3-1393104-8
KRPA-11AY-240=KRPA




TE Part #42563-6
250 FASTON FLAG REC 12-10 AWG
SPBZ




TE Part #690750-5
ANVIL



TE Part #1393105-7
KRPA-5DY-24=KRPA



TE Part #485020-1
SPLICE 6000-8000 .020 TPST



TE Part #11026329-00
44005RC,THERM,ROHS



TE Part #6-1611010-2
3100-30T10999CG=40A 3P 120V MO



TE Part #459722-4
BLADE SHEAR



TE Part #9-1393101-0
KRP-11DG-6=KA/KB/KC/KR

Documents

[Datasheets & Catalog Pages](#)
[Measuring_Single_Wall_Tubing](#)

English

[Selecting_Correct_Tubing_1216](#)
English