

# Product Specification PDF

|                   |                                    |
|-------------------|------------------------------------|
| Date              | <b>Correct as of 10th Jan 2025</b> |
| Brand             | <b>C.K Tools</b>                   |
| Product           | <b>T3120A 05516</b>                |
| Description       | <b>SDS Drill Bit 5.5x90x160mm</b>  |
| Barcode           | <b>5013969249828</b>               |
| Commodity code    | <b>8207503000</b>                  |
| Country of origin | <b>CN</b>                          |



|                     |  |
|---------------------|--|
| Features & Benefits | ~ Tungsten carbide tipped with optimized geometry for drilling concrete and stone ~ Vacuum brazed tips for durability ~ Ground flutes designed for optimum debris removal ~ SDS-plus shank ~ Diameter: 5,5 mm ~ Working length: 90 mm ~ Total length: 160 mm |
| Health & Safety     | Users and bystanders are advised to wear safety goggles  |
| Warranty            | C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.  |

## Product Weights and Measures

|                       | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity         | 1            | 1                           | 10                  | 200               |
| Width mm              | 5.5          | 40                          | 80                  | 180               |
| Depth mm              | 160          | 200                         | 200                 | 420               |
| Height mm             | 5.5          | 6                           | 100                 | 260               |
| Weight                | 39.8         | 43.8                        | 538                 | 11.3              |
| Packaging Information | Card use     | Paper Envelope              | Card box            | Case              |
|                       | Card gms     | 8                           | 60                  | 500               |
|                       | Plastic use  | 0                           | 0                   | -                 |
|                       | Plastic gms  | 0                           | 0                   | 50                |
|                       | Metal use    | 0                           | 0                   | -                 |
|                       | Metal gms    | 0                           | 0                   | 0                 |
|                       | Timber use   | 0                           | 0                   | -                 |
|                       | Timber gms   | 0                           | 0                   | 0                 |