

KCG3Y

Cam switch Operating head, Harmony K, for multifixing, plastic, yellow, 45 x 45 mm, red handle, marked 0-1, 90 degree, padlocking

Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KCG
Product compatibility	Front mounting bodies 12 and 20 A by multifixing
Cam switch head type	With front plate 45 x 45 mm
Type of operator	Red handle, length = 35 mm
Rotary handle padlocking	With
Presentation of legend	With yellow legend, 0 - 1
Switching angle	90 °

Complementary

Mechanical durability	1000000 cycles
CAD overall width	45 mm
CAD overall height	45 mm
CAD overall depth	45 mm
Length	35 mm
Net weight	0.024 kg

Environment

Protective treatment	TC
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
IP degree of protection	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration