

Reflex iC60H Ti24 25 A 4P curve D integrated control MCB

Local distributor code: 399364392

A9C66425

! Discontinued on: 8 Jul 2022

EAN Code: 3606480455278

① Discontinued

Main

Device application	Distribution Control	
Range	Acti9	
product name	Reflex iC60	
Device short name	Reflex iC60H	
Product or component type	Integrated control circuit breaker	
Poles description	4P	
Number of protected poles	4	
Network type	AC	
Trip unit technology	Thermal-magnetic	
Curve code	D	

Complementary

•		
[In] rated current	25 A	
Network frequency	50/60 Hz	
Breaking capacity code	Н	
Breaking capacity	30 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2	
[Ui] rated insulation voltage	500 V AC	
Contact position indicator	Yes	
Control type	Toggle Remote control by pulse ON/OFF button Remote control by continuous command	
Control signal type	Maintained very low voltage Impulse Maintained	
Local signalling	Flashing LED: device overheat Green LED: device ON Flashing LED: device tripped Red LED: fault Flashing LED: device ready	
[Uc] control circuit voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC	
[Us] rated supply voltage	230 V AC at 50/60 Hz	

Mounting mode	Fixed	
Mounting support	35 mm symmetrical DIN rail	
9 mm pitches	13	
Height	84 mm	
Width	117 mm	
Depth	77 mm	
Colour	White	
Mechanical durability	50000 cycles	
Electrical durability	AC-1: 50000 cycles AC 50 Hz	
Provision for padlocking	Padlockable	
Locking options description	Padlock in OFF position	
Earth-leakage protection	Separate block	
Product compatibility	With PLC	

Environment

IP degree of protection	IP20 conforming to IEC 60529	
Pollution degree	3	
Tropicalisation	2	
Relative humidity	93 % at 40 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	11.400 cm
Package 1 Length	16.700 cm
Package 1 Weight	814.900 g
Unit Type of Package 2	S03
Number of Units in Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.897 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	8e8587cb-1e8e-4934-ae0d-4f8ec8c2b050
REACh Regulation	REACh Declaration
PVC free	No

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins