



Save as PDF



Peli protector cases - Protector transport cases - 1650 case



Interior dimensions:
72.5 x 44.5 x 27 cm (29" x 18" x 11")

This case has internal wheel and/or handle wells that will reduce usable area. Please review for each application.

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Fold down handles
- Stainless steel hardware and padlock protectors
- 2 layer Pick 'N' Pluck™ foam with convoluted lid foam
- Personalised nameplate service available
- Unconditionally Guaranteed

Retractable extension handle

4 strong polyurethane wheels with stainless steel bearings



Black

Peli protector cases - Protector transport cases - 1650 case SPECIFICATIONS

Exterior Dimensions (L x W x D)	Interior Dimensions (L x W x D)
80.2 x 52 x 31.6 cm (32" x 20" x 12")	72.5 x 44.5 x 27 cm (29" x 18" x 11")

This case has internal wheel and/or handle wells that will reduce usable area. Please review for each application.

Lid Depth	Bottom Depth	Total Depth
4.6 cm (2")	22.4 cm (8.84")	27 cm (10.65")

Lid Depth	Bottom Depth	Total Depth
4.6 cm (1.81")	22.4 cm (8.84")	27 cm (10.65")

Weight w/Foam	Weight w/o Foam	Buoyancy Max.
12.73 kg. (28.06 lbs)	10.9kg (24.03 lbs.)	82.1 kg (181 lbs.)

Range Temperature	No. of Wheels	Retractable Handle
-40 / 99° C (-40 / 210° F)	4	Yes

Personalized Nameplate Available

1650 Case Certificates

- IP67(1 meter submersion for 30 minutes)
- MIL C-4150J
- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	

Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non-Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1650	Peli protector cases - Protector transport cases - 1650 case

Peli protector cases - Protector transport cases - 1650 case Accessories

Cat. #	Description

