

SUXCEED OFFROAD 2.0 BLACK HIGH

PRODUCT CODE	SIZES	WIDTH	WEIGHT*
67913	36 > 48	11	700 g



100%
metal
free

EN 20345:2022 + A1:2024

S3S	FO	LG	CI	SC	SR
-----	----	----	----	----	----

AREAS OF APPLICATION



COMPOSITION

OUTSOLE	PU2D
SCUFF CAP	PU
UPPER	water-repellent oiled grain leather textile insert reflective elements
CLOSING SYSTEM	laces with eyelets and hook
LINING	3D mesh polyester
TONGUE	water-repellent leather and textile with gussets
TOE CAP	non-metallic composite
PERFORATION- RESISTANT MIDSOLE	non-metallic textile
INSOLE	top in non-woven textile bottom in porous foam



Reflective elements



KEY FEATURES

-  WATER-REPELLENT UPPER DELIVERS ENHANCED PROTECTION AGAINST MOISTURE
-  ULTRA-FLEXIBLE SOLE WITH AN ALL-TERRAIN PROFILE
-  INJECTED SCUFF CAP PROTECTS UPPER FOR EXTENDED PRODUCT LIFE
-  REFLECTIVE ELEMENTS FOR IMPROVED VISIBILITY AND SAFETY
-  PROTECTION AGAINST FINE PERFORATION RISKS UP TO 3.0 MM (PS)

*per foot in size 42

PACKAGING

SALES UNIT	1 pair
QUANTITY PER CARTON	10 pairs

ADDITIONAL REQUIREMENTS

Oil-resistant outsole	FO	Abrasion-resistant scuff cap	SC
Ladder grip (sculted heel)	LG	Slip resistance (ceramic tile floor + glycerine)	SR
Cold-insulating sole	CI		

SUSTAINABILITY



PRODUCT



FREE FROM HARMFUL SUBSTANCES PER **UVEX LIST, EXCEEDING REACH REQUIREMENTS**



LEATHER WORKING GROUP
CERTIFIED RESPONSIBLE LEATHER



2% RECYCLED MATERIALS
ACCORDING WITH ISO 14021

PACKAGING



SHOE BOX MADE FROM
100% RECYCLED MATERIALS



TISSUE PAPER MADE FROM
100% RECYCLED MATERIALS

COMPOSITION



INSOLE	56% recycled materials
--------	------------------------