



Main

Range	PratiKa
Product or component type	Back box
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	3P or 4P

Complementary

[In] rated current	16 A
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Screw: stainless steel
Device mounting	Surface
Mounting mode	Panel-mounted
Net weight	0.26 kg
Base dimension	65 x 85 mm
Height	85 mm
Width	65 mm
Colour	Grey (RAL 7035)




Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Packing Units

Package 1 Weight	258 g
------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
