



Outlet filter, Extract: W: 177 mm, H: 177 mm, RAL 7035, IP54, EMC

Model		
product brand name	SIVACON	
product designation	outlet filter	
type of ventilation	ventilation	
fan design withdrawable fan	No	
design of the product EMC version	Yes	
General technical data		
cutout width	177 mm	
cutout height	177 mm	
Protection class		
protection class IP	IP54	
Appearance		
color	light grey	
Product details		
product component fan	No	
Mechanical Design		
height	204 mm	
width	204 mm	
depth	32 mm	
installation location	Control cabinet...panels, door	
fastening method	screw fixing	
fastening method • 19-inch installation • wall mounting	No Yes	
net weight	0.4 kg	
material	plastic	
ambient temperature during operation • minimum • maximum	-20 °C 65 °C	
Approvals Certificates		
General Product Approval	other	Environment



[Miscellaneous](#)

[Confirmation](#)

[Environmental Con-
firmations](#)

Further information		
Information on the packaging		
https://support.industry.siemens.com/cs/ww/en/view/109813875		

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6400-6GV30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6400-6GV30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6400-6GV30

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

