

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability
- **Flanged Design:** Ensures secure positioning and easy installation
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads
- **Bore Size of 28.02 mm:** Compatible with a wide range of shaft sizes
- **Outside Diameter of 36.06 mm:** Fits standard housing dimensions

RS PRO 28.02 mm Flanged Plain Bearing

RS Stock No: 558-478



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient support for rotating or sliding shafts. Made from sintered bronze, it offers excellent wear resistance and durability, making it ideal for use in various industrial settings.

General Specifications

Bore Size	28.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	36.06 mm
Width	30 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

