

PVC Cable	No. of Cond.	AWG	Jacket Characteristics	ID Number	Ship Wt. (lbs)	Cond. Colors	Shield	UL	CSA	Type	MSHA	Temp. (°C)
	4	26	4.4 mm OD, PVC, YE, 300 V	RF50697-30M RF50697-100M RF50697-200M	2 6 12	BN, WH, BU, BK		•	•	AWM 2517		105° -40°
	5	16	13.2 mm OD, PVC, YE, 600 V	RF50539-30M RF50539-100M RF50539-200M	17 55 110	WH, RD, GN, OG, BK		•	•	STOW	•	105° -40°
	5	16	13.2 mm OD, PVC, YE, 600 V	RF50540-30M RF50540-100M RF50540-200M	17 56 110	RD/BK, RD/WH, RD/BU, GN, RD/OG		•	•	STOW	•	105° -40°
	5	16	13.2 mm OD, PVC, GY, 600 V	RF50680-30M RF50680-100M RF50680-200M	17 54 108	BK, WH, RD, GN, OG		•	•	STOW		105° -40°
	5	18	7.2 mm OD, PVC, YE, 300 V	RF50521-30M RF50521-100M RF50521-200M	6 19 38	RD/BU, GN, RD/OG, RD/BK, RD/WH		•	•	AWM 2517		105° -40°
	5	18	7.2 mm OD, PVC, YE, 300 V	RF50549-30M RF50549-100M RF50549-200M	6 20 39	BK, BU, GN/YE, BN, WH		•	•	AWM 2517	•	105° -40°
	5	18	7.2 mm OD, PVC, GY, 300 V	RF50630-30M RF50630-100M RF50630-200M	6 20 39	BK, BU, GN/YE, BN, WH		•	•	AWM 2517	•	105° -40°
	5	18	7.2 mm OD, PVC, YE, 300 V	RF50578-30M RF50578-100M RF50578-200M	6 19 38	BK, BU, YE, BN, WH		•	•	AWM 2517	•	105° -40°
	5	18	7.0 mm OD, PVC, YE, 300 V	RF51084-30M RF51084-100M RF51084-200M	6 20 40	BN, BK, WH, GY, BU		•	•	AWM 2517		105° -40°
	5	20 22	5.7 mm OD, PVC, GY, 300 V	RF50563-30M RF50563-100M RF50563-200M	4 11 21	22 = BU, BN, WH, BK 20 = GN/YE		•	•	AWM 2517	•	105° -40°
	5	22	5.7 mm OD, PVC, GY, 300 V	RF50609-30M RF50609-100M RF50609-200M	4 11 22	GY, BN, WH, BK, BU, Drain (24)	Foil/Drain	•	•	AWM 2517		105° -40°
	5	22	6.6 mm OD, PVC, GY, 600 V	RF50713-30M RF50713-100M RF50713-200M	6 18 36	BN, WH, BU, BK, GY, Drain (24)	Foil/Drain Braid	•	•	ITC/PLTC AWM 2586		105° -30°
	5	22	5.7 mm OD, PVC, GY, 300 V	RF50543-30M RF50543-100M RF50543-200M	4 11 22	GY, BN, WH, BU, BK		•	•	AWM 2517	•	105° -40°
	5	22	5.7 mm OD, PVC, YE, 300 V	RF50556-30M RF50556-100M RF50556-200M	4 11 22	RD/BK, RD/WH, RD, GN, RD/YE		•	•	AWM 2517	•	105° -40°
	5	22	5.7 mm OD, PVC, YE, 300 V	RF50684-30M RF50684-100M RF50684-200M	4 11 22	BN, WH, GY, BK, BU		•	•	AWM 2517	•	105° -40°
	5	22	6.9 mm OD, PVC, BU, 300 V	RF50767-30M RF50767-100M RF50767-200M	5 15 29	WH, BK, GN, RD, OG		•	•	ITC/PLTC AWM2517		105° -30°
	5	22	5.7 mm OD, PVC, BK, 300 V	RF50982-30M RF50982-100M RF50982-200M	4 11 22	GN, BN, WH, BU, BK		•	•	AWM 2517	•	105° -40°
	6	12	17.7 mm OD, PVC, YE, 600 V	RF51059-30M RF51059-100M RF51059-200M	18 59 117	BK, RD, BU, OG, YE, BN		•	•	AWM 2839 TC-ER		90° -40°
	6	12	15.5 mm OD, PVC, YE, 600 V	RF51286-30M RF51286-100M RF51286-200M	25 83 165	BU, RD, GN, BN, OG, YE	Braid	•	•	AWM 2839 TC-ER		90° -40°
	6	14	10.5 mm OD, PVC, YE, 600 V	RF51078-30M RF51078-100M RF51078-200M	14 45 89	WH, RD, GN, OG, BK, BU		•	•	AWM 2517		105° -40°
	6	16	13.7 mm OD, PVC, YE, 600 V	RF50565-30M RF50565-100M RF50565-200M	17 56 111	WH, BK, GN, OG, RD, BU		•	•	STOW	•	105° -40°