



Visit the website for your country to get more information and discover our products.

 India ▾

[Proceed](#)

HellermannTyton

09/07/2026

Cleaning tissue, 310x270mm, white, 72pcs.

Art.-No. 435-01603 | Reliclean-CO-WH | [Copy item description](#)



- Tissue size 27 x 31 cm
- Strong one-step cleaning action
- Easily removes stubborn dirt
- Binds dirt without leaving any residue
- Reliclean restores natural oils and dries quickly
- Tissue are biodegradable
-
-

[Show more](#) ▾

RoHS ✓





Visit the website for your country to get more information and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026

Base Data

Application	RELICON Reliclean is an antibacterial, degreasing and quickly drying hand cleaning tissue. Suitable especially for workshops, industry and areas where hands and surfaces are strongly soiled. Ideal for cleaning heavily soiled hands, cable sheaths, tools and equipment. Removes e.g. polyurethane, grease, oils, glue, bitumen, wax, soot, ink, sealants, paints, brake dust, coal dust etc.
Colour	White (WH)
Material	Cotton (CO)
PART DESCRIPTION	Reliclean-CO-WH
N	
Package Content	72 pcs.
Product Family	RELICON Reliclean
Product Group	Hand cleaning tissues
Short Description	Hand cleaning tissues 27x31 cm
Technical Description	INGREDIENTS: AQUA, CITRUS AURANTIUM DULCIS PEEL EXTRACT, LIMONENE, C11-12 ISOPARAFFIN, C11-15 SEC-PARETH-12, ISOPROPYL ALCOHOL, PROPYLENE GLYCOL, SODIUM LAURYL SULFATE, BHT, SORBITOL, BENZYL ALCOHOL, POTASSIUM SORBATE, LINALOOL, ETHYLHEXYLGLYCERIN, PERFUME, CINNAMAL, TOCOPHEROL.
Type	Reliclean
Variant	Wet
Weight/Unit	1.046 kg

Product Dimensions

Length (L)	310 mm
Width (W)	270 mm



Visit the website for your country to get more information and discover our products.

Proceed

HellermannTyton

09/07/2026

ROHS compliant Yes

Specifications **RoHS** ✓



Visit the website for your country to get more information and discover our products.

Proceed

HellermannTyton

09/07/2026

Packaging 1 - Height 0.195 m
ht (m)

Packaging 1 - Length 0.165 m
th (m)

Packaging 1 - Qty 1

Packaging 1 - Type pack

Packaging 1 - Volume 0.005308875 m³
me (m³)

Packaging 1 - Weight 1.046 kg
ght (kg)

Packaging 1 - Width 0.165 m
h (m)

Packaging 3 - Height 0.21 m
ht (m)

Packaging 3 - Length 0.5 m
th (m)

Packaging 3 - Qty 6

Packaging 3 - Type carton

Packaging 3 - Volume 0.0352 m³
me (m³)

Packaging 3 - Weight 6.666 kg
ght (kg)

Packaging 3 - Width 0.335 m
h (m)

Packaging 4 - Height 1.194 m
ht (m)

Packaging 4 - Length 1.2 m
th (m)

Packaging 4 - Qty 120

Packaging 4 - Type pallet



Visit the website for your country to get more information and discover our products.

Proceed

HellermannTyton

09/07/2026

Packaging 4 - width 0.8 m
h (m)

More Information

ETIM 7.0 Key	EC002185
ETIM 8.0 Key	EC002185
ETIM 9.0 Key	EC002185

HellermannTyton

 International

Imprint

Policy and Values

Sitemap

Data Protection

Contact

Terms of Service

Guidelines and Commitments

Social Media



Visit the website for your country to get more information
and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026
