

PRODUCT-DETAILS

# OS315BB3LUU4FZ

## OS315BB3LUU4FZ Enclosed switch fuse



### General Information

|                       |                                     |
|-----------------------|-------------------------------------|
| Extended Product Type | OS315BB3LUU4FZ                      |
| Product ID            | 1SCA022320R6700                     |
| EAN                   | 6417019082394                       |
| Catalog Description   | OS315BB3LUU4FZ Enclosed switch fuse |

Long Description

The enclosed switch fuse disconnecter is using a galvanised steel enclosure, with polyester coating. It is suitable for outdoor use with respect to UV light and ingress protection. The enclosure have inbuilt gas pressure relief function to protect the user in case of an internal arc. The door is earthed via the hinges. The enclosure is prepared for single and parallel cables. Cable entry types can be blank , ring-flange or C-flange type (FL21), with different cable configuration, like top/bottom or bottom/bottom. The handle is padlockable for 3 padlocks, cover is interlocked, and interlock function can be bypassed for thermographing.

### Ordering

|                        |              |
|------------------------|--------------|
| Minimum Order Quantity | 1 piece      |
| Customs Tariff Number  | 85363090     |
| Country of Origin      | Finland (FI) |

### Popular Downloads

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SCC340015C0201 |
|-----------------------------------|-----------------|

|                          |                   |
|--------------------------|-------------------|
| Instructions and Manuals | 1SCC340004M0004   |
| Mechanical Drawings      | OTKM804033PBL.stp |

## Dimensions

|                            |          |
|----------------------------|----------|
| Product Net Width          | 400 mm   |
| Product Net Height         | 800 mm   |
| Product Net Depth / Length | 330 mm   |
| Product Net Weight         | 28.54 kg |

## Technical

|  |  |
|--|--|
| Rated Operational Current AC-22A ( $I_g$ ) | (380 ... 415 V) 315 A<br>(690 V) 315 A   |
| Rated Operational Current AC-23A ( $I_g$ ) | (380 ... 415 V) 315 A<br>(690 V) 315 A   |
| Conventional Thermal Current ( $I_{the}$ ) | 315 A  |
| Rated Insulation Voltage ( $U_i$ )         | acc. to IEC/EN 60664-1 1000 V  |
| Rated Operational Voltage                  | 690 V  |
| Power Loss                                 | at Rated Operating Conditions per Pole 19 W                                    |
| Pollution Degree                           | 3  |
| Handle Color                               | Black  |
| Handle Type                                | Pistol handle  |
| Position of Line Terminals                 | Top In - Bottom Out  |
| Fuse Size                                  | B1-B3  |
| Fuse System                                | British Standard   |
| Standards                                  | IEC 60947-1, -3  |
| Number of Poles                            | 4  |
| Connecting Capacity Main Circuit           | Hole Diameter 10 mm<br>Screw Clamp / PE Terminal 4pcs, 10...70 mm <sup>2</sup> |
| Cable Entry Position                       | Up/Down  |
| Cable Outlets Per Side                     | Blank / Blank  |
| Degree of Protection                       | acc. to IEC 60529 IP65   |
| Enclosure Material                         | Steel sheet  |
| Maximum Mounted Auxiliary Contacts         | 2 NO, 1 NC   |
| Mounted Auxiliary Contacts                 | 0 NO, 0 NC   |
| Position of Neutral Terminals              | Top In - Bottom Out  |
| Position of PE Terminals                   | Top In - Bottom Out  |
| Fuse Type                                  | BS   |

## Certificates and Declarations (Document Number)

|                                |                 |
|--------------------------------|-----------------|
| Declaration of Conformity - CE | 1SCC340031D2703 |
|--------------------------------|-----------------|

|                          |                 |
|--------------------------|-----------------|
| Instructions and Manuals | 1SCC340004M0004 |
| RoHS Information         | 1SCC311108D0202 |

## Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | box 1 piece   |
| Package Level 1 Width          | 425 mm        |
| Package Level 1 Depth / Length | 910 mm        |
| Package Level 1 Height         | 415 mm        |
| Package Level 1 Gross Weight   | 30.69 kg      |
| Package Level 1 EAN            | 6417019082394 |

## Classifications

|                            |   |
|----------------------------|---|
| Object Classification Code | Q   |
| ETIM 5                     | EC000216 - Switch disconnecter                              |
| ETIM 6                     | EC000216 - Switch disconnecter                              |
| ETIM 7                     | EC000216 - Switch disconnecter                              |
| WEEE Category              | 4. Large Equipment (Any External Dimension More Than 50 cm) |

## Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Switch Fuses

