

## eco!Booster TR 030

eco!Booster for cold and hot water high-pressure cleaners (nozzle size 030) with 50% more area performance than the Kärcher power nozzle; ideal for delicate surfaces.



Order no. **2.113-084.0**

### Technical data

EAN code		4066529118813
Pressure	bar	max. 300
Temperature	°C	max. 85
Nozzle size		30
Connection thread		EASY!Lock
Weight incl. packaging	kg	0.5



## 50% higher cleaning performance compared to the flat jet

- Thorough, fast and more sustainable cleaning.

## 50% higher water efficiency\*

- Saves water.
- \* Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

## 50% higher energy efficiency\*

- Saves energy.
- \* Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

## COMPATIBLE MACHINES

- HD 4/10 EX Plus Classic
- HD 4/11 C Bp
- HD 4/9 P
- HD 5/17 C
- HD 5/17 CX
- PRO HD 400 Ed